

# Product data sheet

Specifications



## Unica Plus - cover frame (fix. frame) - 1 gang - 3 m - white/white - IP55

MGU11.103.18

⚠ Discontinued on: Feb 21, 2024

⚠ Discontinued

### Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Plus
Number Of Gangs	1 gang
Number Of Modules	3 modules
Fixing Mode	Screws
Colour Tint	White
Side Color	White

### Complementary

Material	ASA + PC: cover plate ASA + PC: frame-fixing frame
Standards	EN 60669-1
Width	126 mm
Height	90 mm
Depth	30 mm
Net Weight	0.095 kg

### Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP55
Environmental Characteristic	Alcohol Acetone Liquid soap Window-cleaning fluid UV resistant Oil Petrol Bleach

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.600 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	11.300 cm
Package 1 Length	13.900 cm
Package 1 Weight	92.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.300 cm
Package 2 Width	13.000 cm
Package 2 Length	18.700 cm
Package 2 Weight	527.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.663 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations