


# Product data sheet

Specifications



## Unica Basic - cover frame - 3 gangs, H71 - white/white

MGU2.006.18

 **Discontinued on:** Dec 31, 2023

 **Discontinued**

### Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Basic
Number Of Gangs	3 gangs horizontal
Fixing Mode	Clip-in
Cover Frame Colour Tint	White
Decoration Colour	White

### Complementary

Material	ASA + PC: decorative frame ASA + PC: intermediate part ASA + PC: cover frame
Standards	EN 60669-1
Height	80 mm
Width	227 mm
Depth	14 mm
Distance Between Centers	71 mm
Net Weight	0.042 kg
Market Segment	Residential Small commercial

### Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Liquid soap UV resistant Oil Alcohol Acetone Petrol Window-cleaning fluid Bleach

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	18.500 cm
Package 1 Width	8.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	44.300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	7.500 cm
Package 2 Width	9.500 cm
Package 2 Length	25.000 cm
Package 2 Weight	284.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	75
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.633 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations