

Product data sheet

Specifications



Unica - replacement lamp - 250 V AC - blue - LED lamp

MGU0.822.AZL

⚠ Discontinued on: Feb 21, 2024

⚠ Discontinued

Main

Range	Unica
Accessory / Separate Part Category	Replacement accessories
Product Or Component Type	Replacement LED
Aesthetic Name	Unica
Light Block Colour	Blue
Bulb Type	LED

Complementary

[Ue] Rated Operational Voltage	127/230 V AC for switch
Current Consumption	0.15 mA
Temperature Rise	Max +15 °C above ambient temperature
Ambient Air Temperature For Operation	-20...40 °C
Net Weight	0.0027 kg

Environment

Standards	UNE 60669-1
-----------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	1.500 cm
Package 1 Length	3.500 cm
Package 1 Weight	2.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.500 cm
Package 2 Width	8.000 cm
Package 2 Length	8.500 cm
Package 2 Weight	55.000 g
Unit Type Of Package 3	S01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	90
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	644.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations