

Product data sheet

Specifications



Unica Top/Class - 1 telephone socket - RJ11 - aluminium

MGU3.490.30

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Telephone socket
Device Presentation	Mechanism
Colour Tint	Aluminium
Telephone Socket Type	RJ11 (4 contacts) - category 3 at 16 Mbit/s

Complementary

Socket Number	1
Number Of Modules	1 module
Connections - Terminals	Screw terminals twisted pair
Fixing Mode	Clip-in
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Depth	23 mm
Width	22.5 mm
Height	45 mm
Embedding Depth	12 mm
Net Weight	0.013 kg
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Oil Bleach Window-cleaning fluid Liquid soap Acetone Alcohol Petrol

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	4.4 cm
Package 1 Length	6.8 cm
Package 1 Weight	18 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.8 cm
Package 2 Width	13.6 cm
Package 2 Length	33.5 cm
Package 2 Weight	226 kg
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	1375 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations