


# Product data sheet

Specifications



## Unica Quadro Pearl - cover frame - 2 gangs, H71/V71 - salmon

MGU4.704.37

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

### Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Quadro
Number Of Gangs	2 gangs horizontal 2 gangs vertical
Fixing Mode	Clip-in
Cover Frame Colour Tint	Salmon

### Complementary

Material	ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	87 mm
Width	158 mm
Depth	14 mm
Distance Between Centers	71 mm
Net Weight	0.028 kg
Market Segment	Small commercial Residential

### Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol UV resistant Bleach Window-cleaning fluid Liquid soap Alcohol Oil Acetone

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.500 cm
Package 1 Width	8.500 cm
Package 1 Length	16.000 cm
Package 1 Weight	26.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	6.500 cm
Package 2 Width	12.500 cm
Package 2 Length	18.500 cm
Package 2 Weight	189.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	20
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	917.000 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations