

# Product data sheet

Specifications



## Unica Top/Class - 1 RJ45 socket (S-One) - 2 m - Cat.5e, S/FTP - graph.

MGU3.413.12

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Data socket
Device Presentation	Mechanism
Colour Tint	Graphite
Data Socket Type	RJ45 8 contact(s) Cat.5e < 155 MHz
Provided Equipment	Label holder Protective flap

### Complementary

Communication Network Type	1000BASE-T
Communication Port Protocol	ATM 155 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	S/FTP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Fixing Mode	Clip-in
Installation Direction	Straight
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Depth	36 mm
Width	85 mm
Height	80 mm
Embedding Depth	25 mm

### Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Oil Window-cleaning fluid UV resistant Bleach Liquid soap Petrol Acetone Alcohol
Standards	ISO 8877

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	4.500 cm
Package 1 Length	4.500 cm
Package 1 Weight	45.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.000 cm
Package 2 Width	18.000 cm
Package 2 Length	18.500 cm
Package 2 Weight	537.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	200
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	11.384 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---