

Product data sheet

Specifications



Unica Top - cover frame (fix. frame) - 2 gangs (H) - 2x6 m - glossy chrome/graph

MGU49.426.238

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Top
Number Of Gangs	2 gangs
Installation Direction	Horizontal
Number Of Modules	2 x 6 modules
Fixing Mode	Screws
Colour Tint	Glossy chrome
Side Color	Graphite

Complementary

Provided Equipment	Fixing frame
Material	ASA + PC: intermediate part LATER 4 G30V0 2307Y1 GRIS: fixing frame Zamak: cover frame
Standards	EN 60669-1
Width	195 mm
Height	175 mm
Depth	16 mm
Distance Between Centers	69 mm
Net Weight	0.344 kg

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Window-cleaning fluid Bleach Liquid soap Petrol Acetone UV resistant Oil

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	17.5 cm
Package 1 Length	19.5 cm
Package 1 Weight	331 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	8 cm
Package 2 Width	20 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.106 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	15
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.017 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations