

Product data sheet

Specifications



Unica - data socket - 1 socket - mini jack - Female - ivory

MGU3.433.25

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Audio socket
Connector Type	Mini-jack
Electrical Circuit Type	Audio
Device Presentation	Mechanism
Colour Tint	Ivory (RAL 9010)
Type Of Packing	Group

Complementary

Device Mounting	Flush
Socket Number	1
Fixing Mode	Clip-in
Number Of Modules	1 module
Surface Finish	Matt
Quantity Per Set	Set of 10
Material	Thermoplastic ABS-UV stabilised: centre plate
Height	45 mm
Width	22.5 mm
Depth	41.7 mm
Embedding Depth	25.7 mm
Net Weight	0.01 kg

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...40 °C
Ip Degree Of Protection	IP21
Ik Degree Of Protection	IK04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Oil
	Petrol
	Alcohol
	Bleach
	UV resistant
	Liquid soap
	Acetone
	Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	21.0 cm
Package 1 Length	4.8 cm
Package 1 Weight	23.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.0 cm
Package 2 Width	10.5 cm
Package 2 Length	23.7 cm
Package 2 Weight	230.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	20
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	685.0 g

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	