

Product data sheet

Specifications



Unica - data socket - 1 socket - mini jack - Female - aluminium

MGU3.433.30

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

| | |
|---------------------------|--------------|
| Range | Unica |
| Product Or Component Type | Audio socket |
| Connector Type | Mini-jack |
| Electrical Circuit Type | Audio |
| Device Presentation | Mechanism |
| Colour Tint | Aluminium |
| Type Of Packing | Group |

Complementary

| | |
|-------------------|---|
| Device Mounting | Flush |
| Socket Number | 1 |
| Fixing Mode | Clip-in |
| Number Of Modules | 1 module |
| Surface Finish | Matt |
| Quantity Per Set | Set of 10 |
| Material | Thermoplastic ABS-UV stabilised: centre plate |
| Height | 45 mm |
| Width | 22.5 mm |
| Depth | 41.7 mm |
| Embedding Depth | 25.7 mm |
| Net Weight | 0.01 kg |

Environment

| | |
|---------------------------------------|------------|
| Ambient Air Temperature For Storage | -5...50 °C |
| Ambient Air Temperature For Operation | -5...40 °C |
| Ip Degree Of Protection | IP21 |
| Ik Degree Of Protection | IK04 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------------------|
| Environmental Characteristic | UV resistant |
| | Oil |
| | Window-cleaning fluid |
| | Petrol |
| | Acetone |
| | Alcohol |
| | Bleach |
| | Liquid soap |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.2 cm |
| Package 1 Width | 5.0 cm |
| Package 1 Length | 8.0 cm |
| Package 1 Weight | 23.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 5.7 cm |
| Package 2 Width | 11.5 cm |
| Package 2 Length | 24.7 cm |
| Package 2 Weight | 289.0 g |
| Unit Type Of Package 3 | S01 |
| Number Of Units In Package 3 | 20 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 15.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 787.0 g |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|--|
| <div><div>✓</div><div>Reach Free Of Svhc</div></div> | |
| <div><div>✓</div><div>Toxic Heavy Metal Free</div></div> | |
| <div><div>✓</div><div>Mercury Free</div></div> | |
| <div><div>✓</div><div>Rohs Exemption Information</div></div> | <div>Yes</div> |
| <div>Reach Regulation</div> | <div>REACH Declaration</div> |
| <div>Eu Rohs Directive</div> | <div>Compliant</div> <div>EU RoHS Declaration</div> |
| <div>China Rohs Regulation</div> | <div>China RoHS declaration</div> <div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div> |
| <div>Weee</div> | <div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div> |