

Product data sheet

Specifications



Unica - Double USB charger - 2.1 A - aluminium

MGU5.418.30ZD

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	USB charger
Device Presentation	Mechanism with fixing frame

Complementary

Device Application	Charger
Device Mounting	Flush
Number Of Modules	2 modules
Type Of Usb Power Supply	USB type A + A
Colour Tint	Aluminium
[Ue] Rated Operational Voltage	100...240 V AC 50/60 Hz +/- 10 %
Power Consumption In W	0.1 W
Nominal Output Power	10.5 W
Input Power	12 W
Service Life In Hours	30000 h 10.5 W
Socket Number	2
Integrated Connection Type	2 USB 2.0 port 5 V DC, maximum load current: 2.1 A
Material	ABS (acrylonitrile butadiene-styrene): centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: internal cover
Protection Type	Short-circuit protection
Number Of Terminals	2 screw terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	2 x 0.75...2 x 2.5 mm ² for rigid cable(s) 2 x 0.75...2 x 2.5 mm ² for flexible cable(s) 2 x 0.75...2 x 2.5 mm ² for stranded cable(s)
Wire Stripping Length	8 mm
Product Compatibility	All devices fulfilling the EN 62684 standard
Fixing Mode	Screws or claws
Type Of Packing	Flow-pack
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-5...50 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	2004/108/EC EU directive 2002/95/EC 2006/95/EC EN 60950-1 ETSI EN 301 489-4 EN 62684
Height	71 mm
Width	71 mm
Depth	42 mm
Embedding Depth	30.8 mm
Net Weight	0.088 kg

Environment

Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	84 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8 cm
Package 2 Width	20 cm
Package 2 Length	22.5 cm
Package 2 Weight	943 g
Unit Type Of Package 3	P06
Number Of Units In Package 3	160
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	26.992 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins