


Product data sheet

Specifications



Unica - data/telephone socket - RJ11 - U/UTP - RJ45 5e - 2 m - white

MGU50.2090.18Z

 **Discontinued on:** Dec 31, 2017

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data/telephone socket
Device Presentation	Mechanism with fixing frame
Telephone Socket Type	RJ11 (4 contacts) - category 3 at 16 Mbit/s
Communication Network Type	Ethernet 1000BASE-T ATM 155 Mbps
Data Socket Type	RJ45 8 contact(s) Cat.5e <= 100 MHz
Number Of Modules	2 modules
Fixing Mode	Long claws
Colour Tint	White (RAL 9003)

Complementary

Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Material	ASA + PC: mechanism cover Zamak: fixing frame
Standards	ISO 8877
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Embedding Depth	24.6 mm
Depth	35.8 mm
Width	70.9 mm
Height	70.9 mm
Net Weight	0.0647 kg

Environment

Ik Degree Of Protection	IK01
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP40
Environmental Characteristic	Oil Window-cleaning fluid Acetone Liquid soap Bleach UV resistant Petrol Alcohol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	67.5 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)