

# Product data sheet

Specifications



## Unica Plus - cover frame - 4 modules - glacier blue/ivory

MGU6.104.554

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

### Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Plus
Number Of Modules	4 modules
Fixing Mode	Clip-in
Cover Frame Colour Tint	Glacier blue
Decoration Colour	Ivory

### Complementary

Material	ASA + PC: intermediate part ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	138 mm
Width	80 mm
Depth	13.7 mm
Net Weight	0.024 kg
Market Segment	Small commercial Residential

### Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol UV resistant Window-cleaning fluid Bleach Alcohol Acetone Oil Liquid soap

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.4 cm
Package 1 Width	1.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	26.8 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	7.0 cm
Package 2 Width	9.0 cm
Package 2 Length	24.0 cm
Package 2 Weight	134.0 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations