

Product data sheet

Specifications



Unica Plus - cover frame - 4 modules - sand/ivory

MGU6.104.567

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Plus
Number Of Modules	4 modules
Fixing Mode	Clip-in
Cover Frame Colour Tint	Sand
Decoration Colour	Ivory

Complementary

Material	ASA + PC: intermediate part ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	138 mm
Width	80 mm
Depth	13.7 mm
Net Weight	0.024 kg
Market Segment	Small commercial Residential

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Oil Liquid soap Alcohol Acetone Bleach UV resistant Petrol Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.4 cm
Package 1 Width	1.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	27 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	7 cm
Package 2 Width	9 cm
Package 2 Length	24 cm
Package 2 Weight	135 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	75
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2512 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations