

Product data sheet

Specifications



Unica Top - cover frame - 3 gangs, H71 - fluorescent green/aluminium

MGU66.006.094

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

| | |
|---------------------------|--|
| Range | Unica |
| Device Application | Mounting |
| Product Or Component Type | Cover frame |
| Aesthetic Name | Unica Top |
| Number Of Gangs | 3 gangs horizontal 3 gangs vertical |
| Fixing Mode | Clip-in |
| Cover Frame Colour Tint | Fluorescent green |
| Decoration Colour | Aluminium |

Complementary

| | |
|--------------------------|---------------------------------|
| Material | ASA + PC: decorative frame |
| Standards | EN 60669-1 |
| Height | 80 mm |
| Width | 232 mm |
| Depth | 14 mm |
| Distance Between Centers | 71 mm |
| Net Weight | 0.118 kg |
| Market Segment | Residential Small commercial |

Environment

| | |
|------------------------------|---|
| Ik Degree Of Protection | IK01 |
| Ip Degree Of Protection | IP20 |
| Environmental Characteristic | Window-cleaning fluid Liquid soap Acetone UV resistant Oil Bleach Petrol Alcohol |

Packing Units

| | |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.500 cm |
| Package 1 Width | 8.000 cm |
| Package 1 Length | 23.500 cm |
| Package 1 Weight | 123.300 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 5.500 cm |
| Package 2 Width | 10.500 cm |
| Package 2 Length | 24.500 cm |
| Package 2 Weight | 426.000 g |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 18 |
| Package 3 Height | 15.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 2.813 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations