

Product data sheet

Specifications



Unica Top - cover frame - 2 gangs - glossy chrome/aluminium

MGU66.004V.038

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Top
Number Of Gangs	2 gangs vertical
Fixing Mode	Clip-in
Cover Frame Colour Tint	Glossy chrome
Decoration Colour	Aluminium

Complementary

Material	ASA + PC: decorative frame ASA + PC: intermediate part
Standards	EN 60669-1
Height	161 mm
Width	80 mm
Depth	14 mm
Distance Between Centers	71 mm
Net Weight	0.087 kg
Market Segment	Small commercial Residential

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Acetone Bleach Liquid soap Window-cleaning fluid Petrol UV resistant Oil Alcohol

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	8.0 cm
Package 1 Length	16.0 cm
Package 1 Weight	97.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	6.5 cm
Package 2 Width	12.7 cm
Package 2 Length	18.3 cm
Package 2 Weight	346.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	48
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.969 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations