

Product data sheet

Specifications



Unica Top - cover frame - 2 gangs - onyx copper/aluminium

MGU66.004V.096

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

| | |
|---------------------------|------------------|
| Range | Unica |
| Device Application | Mounting |
| Product Or Component Type | Cover frame |
| Aesthetic Name | Unica Top |
| Number Of Gangs | 2 gangs vertical |
| Fixing Mode | Clip-in |
| Cover Frame Colour Tint | Onyx copper |
| Decoration Colour | Aluminium |

Complementary

| | |
|--------------------------|---|
| Material | ASA + PC: decorative frame ASA + PC: intermediate part |
| Standards | EN 60669-1 |
| Height | 161 mm |
| Width | 80 mm |
| Depth | 14 mm |
| Distance Between Centers | 71 mm |
| Net Weight | 0.087 kg |
| Market Segment | Residential Small commercial |

Environment

| | |
|------------------------------|---|
| Ik Degree Of Protection | IK01 |
| Ip Degree Of Protection | IP20 |
| Environmental Characteristic | Alcohol UV resistant Bleach Petrol Oil Acetone Liquid soap Window-cleaning fluid |

Packing Units

| | |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.4 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 16.5 cm |
| Package 1 Weight | 94 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 12 cm |
| Package 2 Width | 6.5 cm |
| Package 2 Length | 18.5 cm |
| Package 2 Weight | 350 g |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 24 |
| Package 3 Height | 15 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 3.255 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |