

Product data sheet

Specifications



Unica Top - cover frame - 3 gangs, H71 - cherry tree/aluminium

MGU66.006.0M2

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

Main

Range	Unica
Device Application	Mounting
Product Or Component Type	Cover frame
Aesthetic Name	Unica Top
Number Of Gangs	3 gangs horizontal
Fixing Mode	Clip-in
Cover Frame Colour Tint	Cherry tree
Decoration Colour	Aluminium

Complementary

Material	ASA + PC: decorative frame ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	80 mm
Width	232 mm
Depth	14 mm
Distance Between Centers	71 mm
Net Weight	0.092 kg
Market Segment	Small commercial Residential

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid Liquid soap Petrol Oil Acetone Alcohol Bleach UV resistant

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	9.800 cm
Package 1 Length	24.000 cm
Package 1 Weight	69.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	5.000 cm
Package 2 Width	10.500 cm
Package 2 Length	23.700 cm
Package 2 Weight	282.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	51
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.384 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations