

Product data sheet

Specifications



mini Pragma surface enclosure - 1 x 6 modules - smoked door

MIP10106S

 **Discontinued on:** Jun 30, 2021

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	6
Nb Of Horizontal Rows	1
Type Of Door	Smoked
Width	160 mm outside:
Height	198 mm outside:
Depth	95.5 mm outside:

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	12
Total Number Of 18 Mm Modules	6
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Cable Entry	1 trunking flange 1 bare flange
Terminal Block Function	Without
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Door: smoked Front face: white (RAL 9003)

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	16 cm
Package 1 Length	19.5 cm
Package 1 Weight	429 g

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations