

Product data sheet

Specifications



Socket-outlet, Merten System M, 2P + E, 16A, Schuko, screwless terminals, glossy, polar white

MTN2311-0319

Main

| | |
|-------------------------------|--|
| Aesthetic Name | M-Arc System M M-Plan glass M-Elegance M-Plan M-Star M-Smart |
| Device Presentation | Mechanism with central plate |
| Outlet Standard | German |
| Product Or Component Type | Socket-outlet |
| Socket Additional Information | Shuttered With hinged lid |

Complementary

| | |
|--------------------------------|------------------------|
| Outlet Poles Configuration | 2P + E |
| Wiring Device Mounting | Flush |
| Fixing Mode | By screws and claws |
| Colour Tint | Polar white (RAL 9010) |
| Connections - Terminals | Screwless terminals |
| Rated Current | 16 A |
| [Ue] Rated Operational Voltage | 250 V |

Environment

| | |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.600 cm |
| Package 1 Width | 7.000 cm |
| Package 1 Length | 7.000 cm |
| Package 1 Weight | 84.000 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 9.400 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Package 2 Width | 18.400 cm |
| Package 2 Length | 27.000 cm |
| Package 2 Weight | 952.000 g |
| Unit Type Of Package 3 | CAR |
| Number Of Units In Package 3 | 60 |
| Package 3 Height | 30.600 cm |
| Package 3 Width | 34.100 cm |
| Package 3 Length | 40.500 cm |
| Package 3 Weight | 6.144 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |