

# Product data sheet

Specifications



Socket-outlet, Merten System M, 2P + E, 16A, French, screwless terminals, IP44, glossy, active white

MTN2514-0325

## Main

Range	Merten
Product Name	System M
Aesthetic Name	M-Smart M-Arc M-Elegance M-Plan M-Star
Device Presentation	Mechanism with central plate
Outlet Standard	French
Product Or Component Type	Socket-outlet
Socket Additional Information	Shuttered With hinged lid

## Complementary

Outlet Poles Configuration	2P + E
Wiring Device Mounting	Flush
Fixing Mode	By screws
Colour Tint	Active white (RAL 9016)
Connections - Terminals	Screwless terminals
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Socket Number	1

## Environment

Ip Degree Of Protection	IP44
-------------------------	------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.700 cm
Package 1 Width	7.600 cm
Package 1 Length	7.700 cm
Package 1 Weight	100.000 g
Unit Type Of Package 2	CAR

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	50
Package 2 Height	19.700 cm
Package 2 Width	30.900 cm
Package 2 Length	40.900 cm
Package 2 Weight	5.342 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations