


Product data sheet

Specifications



Double pbutton insrt two-way 1 pole, flush-mntd, 10 A, AC 250 V, screwl. term.

MTN3159-0000

Main

Range Of Product	Merten inserts
Product Or Component Type	Push-button
Device Presentation	Mechanism

Complementary

Switch Function	1-pole 2-way
Control Type	Rocker
Device Mounting	Flush
Fixing Mode	By screws and claws
[Ue] Rated Operational Voltage	250 V
[In] Rated Current	10 A
Number Of Rocker	2
Contacts Type And Composition	C/O
Connections - Terminals	Screwless terminals
Material	Metal Plastic

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	7.100 cm
Package 1 Length	7.200 cm
Package 1 Weight	66.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.100 cm
Package 2 Length	27.300 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	762.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	40
Package 3 Height	19.900 cm
Package 3 Width	30.600 cm
Package 3 Length	40.400 cm
Package 3 Weight	3432.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations