

# Product data sheet

Specifications



One asymmetric mounting rail  
32x15 L 2000mm, Order by  
Multiples of 10 units

NSYADR200

## Main

|                                    |                       |
|------------------------------------|-----------------------|
| Anwendung                          | Multi-purpose         |
| Range                              | Spacial               |
| Product Or Component Type          | Rail                  |
| Accessory / Separate Part Category | Mounting accessory    |
| Type Of Rail                       | Asymmetrical DIN rail |
| Enclosure Nominal Dimensions       | -                     |
| Range Compatibility                | Spacial<br>Thalassa   |
| Device Composition                 | 1 rail                |
| Quantity Per Set                   | Set of 10             |

## Complementary

|                |   |
|----------------|---|
| Material       | Galvanised steel                                    |
| Surface Finish | Not perforated                                      |
| Fixing Mode    | By fixing element - structure of enclosure location |
| Adjustment     | Continuous adjustment<br>Pitch 25 mm                |
| Length         | 2000 mm   |
| Height         | 15 mm nominal:                                      |
| Width          | 32 mm nominal:                                      |
| Thickness      | 1.5 mm  |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 15.0 cm   |
| Package 1 Width              | 32.0 cm   |
| Package 1 Length             | 2000.0 cm |
| Package 1 Weight             | 1.45 kg   |
| Unit Type Of Package 2       | CAR       |
| Number Of Units In Package 2 | 20        |
| Package 2 Height             | 7.6 cm    |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 2 Width              | 9.0 cm   |
| Package 2 Length             | 201.0 cm |
| Package 2 Weight             | 29.0 kg  |
| Unit Type Of Package 3       | PAL      |
| Number Of Units In Package 3 | 600      |
| Package 3 Height             | 50.0 cm  |
| Package 3 Width              | 200.0 cm |
| Package 3 Length             | 120.0 cm |
| Package 3 Weight             | 870.0 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |