


Product data sheet

Specifications



Lower sup. Ver. Busbars In 3200A
10mm bars. Bar distance 115mm.
For 800mm widths

NSYAS800L

Main

Range	Spacial
Accessory / Separate Part Category	Support accessory
Product Or Component Type	Bar support
Anwendung	Multi-purpose Prisma application
Enclosure Nominal Dimensions	-
Mounting Location	Bottom
Busbar Position	Vertical
Range Compatibility	Lineryg Linergy LGYE Lineryg Linergy BS Spacial Spacial SFP

Complementary

Cubicle-Device Connection	Lineryg LGYE lateral busbar Lineryg BS lateral busbar
Device Composition	fixing elements 1 insulating bar support 1 metal support
Quantity Per Set	Set of 1
Material	Bar support: plastic Metal support: steel
Fixing Mode	By fixing element - bottom frame of enclosure location
Height	66 mm
Width	750 mm fixing centers: 800 mm nominal:
Depth	39 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	10.0 cm
Package 1 Length	78.5 cm
Package 1 Weight	2.188 kg
Unit Type Of Package 2	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	50
Package 2 Height	45.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	125.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations