


Product data sheet

Specifications

19" fixed shelf 1U on 2 uprights D250 with permissive load 15Kg



NSYBF1U25P

Overview

Presentation	Power Management
Lead Time	Usually Ships within 4 Weeks

Main

Range Of Product	Actassi
Product Or Component Type	Fixed shelf
Accessory / Separate Part Type	Fixed perforated shelf
Device Application	Multi-purpose Electronic application
Colour	Grey (RAL 7035)

Complementary

Range Compatibility	Actassi VDA Actassi VDS
Material	Sheet steel
Surface Finish	Epoxy-polyester powder
Mounting Support	19" rack, front or rear
Product Compatibility	Spacial SF-S, SF-E, VDM, PLA enclosures
Fixing Mode	By 19" fixing element: 19" uprights of rack
Number Of Rack Unit	1U
Permanent Permissible Load	15 kg
Thickness	5 mm
Number Of Units 19"	1
Height	44.45 mm
Width	465 mm
Depth	250 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.65 cm
Package 1 Width	23.11 cm
Package 1 Length	50.04 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.73 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	42
Package 2 Height	73 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	85 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations