

Product data sheet

Specifications



Climasys CC - electronic
hygrotherm - 9 -30V - temp -40...
80°C - Hr 20...80%

NSYCCOHT30VID

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Electronic hygrotherm
Temperature Setting Range	-40...80 °C
Humidity Setting Range	20...80 %
Display Type	OLED screen
Information Displayed	Relative humidity Temperature in °C Temperature in °F

Complementary

Input Voltage	9...30 V AC/DC
Sensor Type	Optional NTC external sensor
Maximum Switching Capacity	4 A 30 V AC/DC
Electrical Connection	8 connectors, clamping capacity: 2.5 mm²
Mounting Mode	Clipped By screws
Height	85 mm external:
Width	56 mm external:
Depth	44 mm external:
Mounting Location	On mounting plate 35 mm DIN rail Cross rails Spacial upright
Ambient Air Temperature For Operation	-40...80 °C
Hysteresis	2 K programmed value
Hysteresis	3 %
Number Of Outputs	2 ventilation/heating function
Material	PC
Colour	Light grey
Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UR

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	140.0 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	75
Package 2 Height	40.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	11.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations