

Product data sheet

Specifications

Tubes, square 50 mm, length: 2m.
For SPACIAL S3CM HMI encl.



NSYCMT5020

Main

Range	Spacial
Accessory / Separate Part Category	Cable management accessory
Product Or Component Type	Tube
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Between fixing supports and fittings
Mounting Support	Fitting Fixing on support Fixings on enclosure
Range Compatibility	Spacial Spacial S3CM
Device Composition	1 tube
Quantity Per Set	Set of 1

Complementary

Material	Extruded steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	Direct fixing - on fixing supports and fittings location
Permanent Permissible Load	0 kg
Linear Load	6.5 kg/m
Length	2000 mm
Height	2000 mm
Width	50 mm
Thickness	4 mm
Net Weight	14 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	7 cm
Package 1 Length	202 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	14.078 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	30
Package 2 Height	38 cm
Package 2 Width	202 cm
Package 2 Length	120 cm
Package 2 Weight	449.72 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations