

Product data sheet

Specifications



Mounting pillar for Spacial S3D encl. RAL7035. H800m.

NSYCOCN80

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Support pillar device
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Bottom face of the enclosure
Mounting Support	With adaptation plate
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN
Device Composition	fixing elements 1 support pillar
Quantity Per Set	Set of 1

Complementary

Material	Extruded aluminium
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element - on adaptation plate location
Permanent Permissible Load	0 kg
Height	800 mm nominal: 743 mm foot height: 55 mm base height:
Width	370 mm base width: 330 mm fixing centers to floor: 102 mm foot width:
Depth	250 mm base depth: 160 mm fixing centers to floor: 65 mm foot depth:
Net Weight	3.8 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.000 cm
Package 1 Width	27.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	75.500 cm
Package 1 Weight	4.059 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	45.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	44.472 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations