

# Product data sheet

Specifications

## Actassi - 19" plain plate - 4U - aluminium - 3 mm



NSYCRTA4U

 To be discontinued on: Jun 30, 2024

 To be discontinued

### Main

|                                    |                            |
|------------------------------------|----------------------------|
| Range Of Product                   | Actassi                    |
| Product Or Component Type          | 19" front panel            |
| Accessory / Separate Part Category | Cable management accessory |
| Colour                             | Grey (RAL 7035)            |

### Complementary

|                       |  |
|-----------------------|--|
| Mounting Location     | On vertical uprights   |
| Number Of Rack Unit   | 4U   |
| Mounting Support      | 19" rack, front or rear                                      |
| Product Compatibility | Spacial SF-S, SF-E, VDM, PLA enclosures<br>Actassi enclosure |
| Material              | Aluminium  |
| Surface Finish        | Anodized   |
| Product Destination   | Enclosure  |
| Thickness             | 3 mm   |
| Fixing Mode           | By 4 screws  |
| Number Of Units 19"   | 4  |
| Depth                 | 3 mm   |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 0.5 cm   |
| Package 1 Width              | 22.0 cm  |
| Package 1 Length             | 50.0 cm  |
| Package 1 Weight             | 742.0 g  |
| Unit Type Of Package 2       | PAM      |
| Number Of Units In Package 2 | 200      |
| Package 2 Height             | 100.0 cm |
| Package 2 Width              | 100.0 cm |
| Package 2 Length             | 120.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

|                  |          |
|------------------|----------|
| Package 2 Weight | 180.0 kg |
|------------------|----------|

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|  |   |
|--|---|
|  Mercury Free               |   |
|  Rohs Exemption Information | <a href="#">Yes</a>   |
| Reach Regulation   | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive  | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |