

# Product data sheet

Specifications



## DLP modular dist chassis 152modules(18mm) insulating material for PLA H1500xW500

NSYDLP152G

### Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Application	Modular distribution application Multi-purpose
Product Or Component Type	Chassis
Device Short Name	DLP
For Enclosure Nominal Dimensions	-
Mounting Location	Front of enclosure
Range Compatibility	Thalassa Thalassa PLA Thalassa Thalassa PHD
Device Composition	1 chassis structure 1 neutral/earth strip 2 x 16 mm² 5 x 6 mm² 1 plain front panel 8 front panels with 35 mm DIN rail
Additional Information	IP2x not respected when chassis is mounted at 67 mm

### Complementary

Material	Front panel: self-extinguishing Chassis structure and rails: galvanised steel
Colour	Front panel: grey (RAL 7035)
Fixing Mode	By fixing element - on front with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number Of Horizontal Rows	8
Total Number Of 18 Mm Modules	152
Type Of Front Plate	Plain and cut-out plates
Number Of Cut-Out	8 cut-outs
Height	1500 mm
Width	500 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	42.1 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	143.2 cm
Package 1 Weight	4.8 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations