

# Product data sheet

Specifications



## Symmetrical mounting chassis (7 rails) for enclosure dimensions H1200xW800mm

NSYMD128

### Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Chassis
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Symmetrical DIN
Enclosure Nominal Dimensions	-
Mounting Support	Spacer Direct fixing on backstuds Step slide
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Device Composition	fixing elements 2 upright 7 DIN rail
Quantity Per Set	Set of 1

### Complementary

Material	Uprights: aluminium Rail: steel
Fixing Mode	Screwed on backstuds By fixing element
Adjustment	On step slides, type NSYSDCR..., pitch 12.5 mm
Height	1152.4 mm real: 1200 mm nominal:
Width	800 mm nominal: 750 mm real:
Depth	30 mm real:

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	10.0 cm
Package 1 Length	115.5 cm
Package 1 Weight	6.38 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	29.0 cm
Package 2 Width	37.5 cm
Package 2 Length	120.0 cm
Package 2 Weight	63.8 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations