


# Product data sheet

Specifications



## Plain mounting plate H500xW400mm made of galvanised sheet steel

NSYMM54

### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 500 mm W: 400 mm
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Galvanised steel

### Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	90 kg
Height	450 mm
Width	350 mm
Thickness	1.8 mm
Net Weight	2.27 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.2 cm
Package 1 Width	35.0 cm
Package 1 Length	45.5 cm
Package 1 Weight	2.27 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	140
Package 2 Height	37.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	345.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations