

Product data sheet

Specifications



Hinged plain cover plate, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure W800mm steel, H200mm

NSYMPCH208

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Cover plate
Anwendung	Multi-purpose
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Nominal Dimensions Of The Housing	- H: 200 mm W: 800 mm
Mounting Location	On chassis coupling set
Device Composition	fixing elements 1 cover plate hinges
Quantity Per Set	Set of 1

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws
Type Of Front Plate	Hinged plain
Height	200 mm nominal: 199.5 mm real:
Width	800 mm nominal: 678 mm fixing centers: 702 mm real:
Depth	12 mm real:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	20.5 cm
Package 1 Length	75.0 cm
Package 1 Weight	2.492 kg
Unit Type Of Package 2	PAM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	70
Package 2 Height	50.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	187.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations