


Product data sheet

Specifications



Monobloc perforated plates H1000xW600mm with universal perforations 11x26mm

NSYMR106

Main

| | |
|------------------------------------|---|
| Range | Spacial |
| Accessory / Separate Part Category | Mounting accessory |
| Product Or Component Type | Mounting plate |
| Device Application | Multi-purpose |
| Enclosure Nominal Dimensions | - H: 1000 mm W: 600 mm |
| Mounting Location | Direct fixing on backstuds Step slide |
| Mounting Plate Description | Telequick perforated |
| Range Compatibility | Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X |
| Quantity Per Set | Set of 1 |
| Material | Steel |
| Surface Finish | Zinc coated |

Complementary

| | |
|-----------------------|---|
| Fixing Mode | Screwed on backstuds - screw type M8 By fixing element |
| Height | 945 mm |
| Width | 551 mm |
| Depth | 15 mm |
| Thickness | 2 mm |
| Net Weight | 4.04 kg |
| Number Of Slots | 1088 |
| Variant Particularity | Installation in rear of enclosure |
| Cut-Out Dimensions | 11 x 26 mm |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2 cm |
| Package 1 Width | 55.5 cm |
| Package 1 Length | 94.5 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Package 1 Weight | 3.818 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 100 |
| Package 2 Height | 89 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 120 cm |
| Package 2 Weight | 398.5 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |