

# Product data sheet

Specifications



Screwed-on cut-out cover plate,  
PanelSeT SFN, PanelSet SF and  
SM, for electrical enclosure  
W600mm, 2 cut outs, H400mm

NSYMUC406

## Main

Range	PanelSeT
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Cover plate
Anwendung	Multi-purpose
Range Compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM
Nominal Dimensions Of The Housing	- H: 400 mm W: 600 mm
Mounting Location	On chassis coupling set
Device Composition	fixing elements 1 cover plate
Quantity Per Set	Set of 1

## Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws
Number Of Horizontal Rows	2
Total Number Of 18 Mm Modules	48
Type Of Front Plate	With cut-out
Number Of Cut-Out	2 cut-outs
Height	400 mm nominal: 399.5 mm real:
Width	600 mm nominal: 478 mm fixing centers: 502 mm real:
Depth	12 mm real:

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	41.0 cm
Package 1 Length	51.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	2.902 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	100
Package 2 Height	53.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	303.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information