


Product data sheet

Specifications



Spacial SF/SM partial 19" fixed rack - 400 mm

NSYRCKP8

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application
For Enclosure Nominal Dimensions	- H: 400 mm
Rack Type	Partial fixed
Mounting Location	Top front of enclosure
Mounting Support	Cross rails
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 2 upright
Quantity Per Set	Set of 1
Number Of Units 19"	8

Complementary

Material	Steel
Enclosure/Cubicle Description	Floor-standing enclosure
Surface Finish	Zinc coated
Fixing Mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Permanent Permissible Load	2 kg per unit
Height	400 mm
Depth	60 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	11.5 cm
Package 1 Length	37.5 cm
Package 1 Weight	1.326 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	29.0 cm
Package 2 Width	37.5 cm
Package 2 Length	120.0 cm
Package 2 Weight	26.52 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations