

# Product data sheet

Specifications



## Spacial SF/SM 19" swing rack - 1800x800 mm - 36 modules

NSYRSW36

### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application
For Enclosure Nominal Dimensions	- H: 1800 mm
Rack Type	Swing off-centred
Mounting Location	On structure of enclosure
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 2 800 mm swing rack supports 1 hinged rack 1 side lid with handle
Quantity Per Set	Set of 1
Number Of Units 19"	36

### Complementary

Material	Steel
Enclosure/Cubicle Description	Floor-standing enclosure
Surface Finish	Zinc coated
Lock Type	Handle with ball lock
Fixing Mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Colour	Side plate: grey (RAL 7035)
Permanent Permissible Load	3.75 kg per unit with a maximum of 150 kg
Opening Of The 19" Racks	Reversible 120 °
Height	1800 mm
Width	800 mm
Depth	1701 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	11.0 cm
Package 1 Width	73.0 cm
Package 1 Length	170.1 cm
Package 1 Weight	27.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations