

Product data sheet

Specifications



Spacial SF/SM partial 19" swing rack - 1002 mm

NSYRWP21

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application
For Enclosure Nominal Dimensions	- H: 1002 mm
Rack Type	Partial swing
Mounting Location	Front of enclosure
Mounting Support	Partial 19" swing rack support
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	1 rack
Number Of Units 19"	21

Complementary

Material	Steel
Enclosure/Cubicle Description	Floor-standing enclosure
Surface Finish	Zinc coated
Lock Type	Lock 5 mm double bar
Fixing Mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Permanent Permissible Load	2 kg per unit
Opening Of The 19" Racks	Reversible 120 °
Height	1002 mm
Width	600 mm
Depth	1002 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	51.2 cm
Package 1 Length	100.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	4.3 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	15
Package 2 Height	125.5 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	84.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations