

Product data sheet

Specifications



SDX control desk, stainless 304L,
Scotch Brite® finishing,
H1000xW600xD500mm.

NSYSDX6

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Spacial
Product Name	Spacial SDX
Enclosure Type	Multi-purpose
Category	Control desk
Nominal Height	1000 mm
Nominal Width	600 mm
Nominal Depth	500 mm
Product Installation	Floor-standing
Product Destination	Dialogue components
Device Composition	1 structure 1 rear panel 1 lock: door 4 adjustment rail 1 cable gland plate 2 pneumatic stay: desk lid 1 door 3 blanking cover: on top of control desk

Complementary

Body Type	Single piece structure folded and welded
Door Type	Plain
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Plain
Accessibility For Operation	Front Rear
Removable Parts	Door by hinges Rear panel by screws Cable gland plate by clips
Material	Structure, door and rear panel: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface Finish	Structure, door and rear panel: Scotch-Brite® brushed Lock: chromium plated
Thickness	1.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Specific hygiene Corrosive
Net Weight	43 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	61.5 cm
Package 1 Width	61.5 cm
Package 1 Length	114.5 cm
Package 1 Weight	43.0 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	2
Package 2 Height	116.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	125.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile