


Product data sheet

Specifications



Universal cross rails, PanelSeT SFN, Spacial SF, Spacial SM, H90 W400mm, 3 rows, set of 2

NSYSUCR9040

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Universal cross rail
Application	Multi-purpose
Nominal Dimensions Of The Housing	- H: 400 mm

Complementary

Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Mounting Location	On structure of enclosure Between cross rails
Mounting Support	Adaptation profile, on SM enclosures
Device Composition	fixing elements 2 cross rails 4 supports
Quantity Per Set	Set of 1
Material	Steel
Surface Finish	Galvanized
Fixing Mode	By screws
Adjustment	Adjustable with a pitch of 25 mm
Number Of Horizontal Rows	3
Maximum Load	120 kg
Height	Nominal: 400 mm Useful: 307 mm
Width	90 mm
Depth	27 mm
Thickness	1.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.0 cm
Package 1 Width	9.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	6.0 cm
Package 1 Weight	1.15 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	36
Package 2 Height	100.0 cm
Package 2 Width	120.0 cm
Package 2 Length	100.0 cm
Package 2 Weight	41.4 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations