

Product data sheet

Specifications



Spacial S3D flexicable gland plate with membrane pearcable 178 x 63 mm

NSYTLCME

Main

Range	Spacial
Product Or Component Type	Flexicable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial SF Spacial Spacial S3D
Mounting Location	Enclosure bottom
Cable Gland Type	Pierceable by screwdriver
Type Of Gland Plate	Membrane
Cable Outer Diameter	10...26 mm
Cable Entry	Without
Device Composition	1 plate membrane
Quantity Per Set	Set of 1
Material	Plate: steel Membrane: HCE (heat curable elastomer)

Complementary

Colour	Plate: grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Height	30 mm
Width	245 mm 260 mm real:
Depth	130 mm
Net Weight	0.536 kg
Thickness	1.5 mm
Number Of Cut-Out	Undrilled
Cut-Out Dimensions	178 x 63 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	13.5 cm
Package 1 Length	26.0 cm
Package 1 Weight	536.0 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	250
Package 2 Height	62.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	146.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations