

Product data sheet

Specifications



Plug-in bridge, Linergy TR, 10 points, for 2.5mm² terminal blocks, red, 10 way, set of 10

NSYTRAL210

Main

| | |
|------------------------------------|---|
| Range | Linergy |
| Product Name | Linergy TR |
| Product Or Component Type | Plug-in bridge |
| Device Short Name | TRA |
| Accessory / Separate Part Category | Connection accessory |
| Product Compatibility | TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block |
| Number Of Ways | 10 ways |

Complementary

| | |
|-----------------------------|-----------------------|
| Cable Cross Section | 2.5 mm ² |
| Number Of Connections | 2 3 4 |
| Number Of Measurement Input | 3 1 2 4 6 |
| Quantity Per Set | Set of 10 |
| Net Weight | 9 g |
| Colour | Red |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.0 cm |
| Package 1 Width | 15.0 cm |
| Package 1 Length | 17.0 cm |
| Package 1 Weight | 8.0 g |
| Unit Type Of Package 2 | BAG |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 5.0 cm |

| | |
|------------------------------|----------|
| Package 2 Length | 17.0 cm |
| Package 2 Weight | 88.0 g |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 800 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 7.352 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Circularity Profile

No need of specific recycling operations
