

# Product data sheet

Specifications



## Component carrier, Linergy TR, for 5x20mm fuse, 6.2mm width, black

NSYTRASF520

### Main

Range	Linergy
Product Name	TR
Product Or Component Type	Component carrier
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal - removable carrier disconnect terminal block TRR spring terminal - removable carrier disconnect terminal block TRP push-in - removable carrier disconnect terminal block
Length	28 mm
Thickness	6.2 mm

### Complementary

Fuse Size	5 x 20 mm
Cable Cross Section	2.5 mm <sup>2</sup> 4 mm <sup>2</sup>
Number Of Connections	2 1
Number Of Terminals	2 3
Number Of Measurement Input	1 0
Mounting Mode	Plug-in
Quantity Per Set	Set of 10
Net Weight	3.85 g
Colour	Black

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	3.0 cm
Package 1 Length	3.7 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	10
Package 2 Height	2 cm
Package 2 Width	6 cm
Package 2 Length	10.5 cm
Package 2 Weight	40 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	1000
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.318 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	