

Product data sheet

Specifications



Cable passages IP65, round, M63, w/o connectors, 13 entries.

NSYTSAM6313SE

 **Discontinued on:** Aug 31, 2023

 **Discontinued**

Main

Range	Spacial
Product Or Component Type	Quick entrance plate
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box Spacial Spacial S3HD compact enclosure
Device Composition	1 circular plate
Quantity Per Set	Set of 10

Complementary

Mounting Support	Cable gland plate Body of enclosure
Material	Polyamide
Fixing Mode	Clipped By screws
Total Cable Entry Number	13
Cable Entry Number	1 x 6...10 mm 6 x 3.6...6.5 mm 6 x 3...5.5 mm
Height	34 mm real:
Cable Outer Diameter	71 mm 63.5 mm
Net Weight	0.7 kg

Environment

Ip Degree Of Protection	IP65
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	30.0 cm
Package 1 Width	15.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	700.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations