

Product data sheet

Specifications



Wall-Mounted Monobloc 4U W310 D280 Fixed 10" Glazed Door R7035

NSYVDH4UF

⚠ Discontinued on: Dec 3, 2020

⚠ Discontinued

Main

Range	Actassi
Product Name	Actassi XS-E
Product Or Component Type	10" enclosure
Device Application	Small office Home office
Applications	To protect network connectivity equipment To mount 10" equipment
Enclosure Type	1 body
Support Equipment	2 x 10" uprights recessed of 60mm from the front (pitch 12.5 mm)
Front Face	Glazed door
Door Type	Front tinted transparent door - with 1 point locking system (key: 410) - top
Accessibility For Operation	Rear Top Front Side
Colour	Light grey (RAL 7035)

Complementary

Device Composition	3 x cable entries 1 x monobloc structure 1 x tinted transparent cover front 2 x 10" uprights front
Back Face	Plain door
Number Of Cut-Out	1 cut-outside 1 cut-outbottom 1 cut-outtop
Installation Mode	Wall mounted
Material	Sheet steel: structure Sheet steel: door Galvanized steel: upright
Surface Finish	Epoxy-polyester powder
Width	301 mm
Height	290 mm
Depth	201 mm
Net Weight	4.32 kg
Number Of Rack Unit	4U

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Targeted Region	Europe
-----------------	--------

Environment

Ik Degree Of Protection	IK10 conforming to IEC 62262
-------------------------	------------------------------

Ip Degree Of Protection	IP20 conforming to IEC 60529
-------------------------	------------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations