

Product data sheet

Specifications



19" swing chassis 11U PanelSet

NSYVDM11UP

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Multi-purpose Electronic application
For Enclosure Nominal Dimensions	- H: 600 mm W: 600 mm D: 200 mm - H: 600 mm W: 600 mm D: 250 mm - H: 600 mm W: 600 mm D: 300 mm - H: 600 mm W: 600 mm D: 400 mm
Rack Type	Swing
Mounting Location	Front of enclosure
Range Compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial VDM Spacial Spacial CRN
Device Composition	fixing elements 1 19" swing chassis 2 lock
Number Of Units 19"	11

Complementary

Material	Chassis: steel
Enclosure/Cubicle Description	Wall-mounted enclosure
Surface Finish	Epoxy-polyester powder
Lock Type	Lock with 3 mm double bar insert
Fixing Mode	By fixing element
Colour	Grey (RAL 7035)
Permanent Permissible Load	3 kg per unit
Opening Of The 19" Racks	Reversible 120 °
Height	600 mm nominal:
Width	600 mm nominal:
Depth	630 mm
Net Weight	5.41 kg

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	58.0 cm
Package 1 Length	63.0 cm
Package 1 Weight	5.41 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations