


Product data sheet

Specifications



Wall rack VDM 4U swi chass D400

NSYVDM4U4P

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Spacial
Product Name	Spacial VDM
Application	Electronic application
Product Or Component Type	Compact enclosure
Body Type	1-body
Rack Type	Swing
Enclosure Nominal Height	300 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	400 mm
Installation Accessory Type	Wall-mounting
Product Destination	Electronics and networks
Device Composition	1 cable gland plate: bottom 2 lock: 19" swing rack 1 body 1 door with lock 1 19" swing rack

Complementary

Door Type	Glazed
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Number Of Units 19"	4
Accessibility For Operation	Front
Removable Parts	Door by hinges Rack by fixing element
Material	Enclosure and 19" rack: steel
Surface Finish	Enclosure and 19" rack: epoxy-polyester powder
Colour	Enclosure and 19" rack: grey (RAL 7035)
Standards	IEC 62208
Net Weight	16.11 kg
Width	600 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	300 mm
Depth	400 mm

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.0 cm
Package 1 Width	42.5 cm
Package 1 Length	61.0 cm
Package 1 Weight	16.11 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	18
Package 2 Height	208.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	303.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile