

# Product data sheet

Specifications



Cover plate, Linergy TR, 3 points,  
2.2mm width, for spring terminals  
NSYTRR63, grey, Set of 50

NSYTRACR63

 To be discontinued on: Jun 30, 2024

 To be discontinued

## Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Cover plate
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRR spring terminal terminal block, length = 90.5 mm
Thickness	2.2 mm

## Complementary

Cable Cross Section	6 mm <sup>2</sup>
Number Of Connections	3
Number Of Measurement Input	2
Quantity Per Set	Set of 50
Net Weight	3.2 g
Colour	Grey

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	19 cm
Package 1 Length	30 cm
Package 1 Weight	4 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	50
Package 2 Height	19 cm
Package 2 Width	5 cm
Package 2 Length	30 cm
Package 2 Weight	228 g
Unit Type Of Package 3	S01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	200
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	1.088 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)