

Product data sheet

Specifications



Cable passage IP65 w/o connectors, 17 entries.

NSYTSA2417SE

Main

Range	Spacial
Product Or Component Type	Quick entrance plate
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box Spacial Spacial S3HD compact enclosure
Device Composition	1 fixing elements 1 plate
Quantity Per Set	Set of 1

Complementary

Mounting Support	Cable gland plate Body of enclosure
Material	Polyamide
Fixing Mode	By fixing element
Total Cable Entry Number	17
Cable Entry Number	17 x 5...9.2 mm
Height	14 mm real:
Width	146 mm real: 112 mm cut-out: 130 mm fixing center:
Depth	58 mm real: 36 mm cut-out: 32 mm fixing centre:
Net Weight	0.164 kg

Environment

Ip Degree Of Protection	IP65
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.5 cm
Package 1 Width	8 cm
Package 1 Length	16.5 cm
Package 1 Weight	164 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	20 cm
Package 2 Width	20 cm
Package 2 Length	30 cm
Package 2 Weight	1.684 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	400
Package 3 Height	50 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	85 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations