


# Product data sheet

Specifications



## Wall rack VDM 7U swi chass D400

NSYVDM7U4P

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range	Spacial
Product Name	Spacial VDM
Application	Electronic application
Product Or Component Type	Compact enclosure
Body Type	1-body
Rack Type	Swing
Enclosure Nominal Height	400 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	400 mm
Installation Accessory Type	Wall-mounting
Product Destination	Electronics and networks
Device Composition	1 cable gland plate: bottom 2 lock: 19" swing rack 1 body 1 door with lock 1 19" swing rack

### Complementary

Door Type	Glazed
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Number Of Units 19"	7
Accessibility For Operation	Front
Removable Parts	Door by hinges Rack by fixing element
Material	Enclosure and 19" rack: steel
Surface Finish	Enclosure and 19" rack: epoxy-polyester powder
Colour	Enclosure and 19" rack: grey (RAL 7035)
Standards	IEC 62208
Net Weight	18.78 kg
Width	600 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	400 mm
Depth	400 mm

## Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	63.0 cm
Package 1 Width	42.0 cm
Package 1 Length	42.0 cm
Package 1 Weight	18.78 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>