

Product data sheet

Specifications



TV/FM/SAT socket, New Unica, mechanism with fixing frame, 2 modules, male IEC 9.52 mm, IP20, white

NU545018F

Main

Range	New Unica
Product Or Component Type	TV/FM/SAT socket
Device Application	Communication Media device support
Device Presentation	Mechanism with fixing frame
Tv Socket Type	Individual
Colour Tint	White (RAL 9003)
Condition Of Use	Indoor

Complementary

Tv Connector	Male IEC 9.52 mm
Radio Connector	Female IEC 9.52 mm
Sat Connector	F type
Device Composition	Support ring
Path Attenuation	2 dB TV/VHF signal47...75 MHz 2 dB TV/UHF signal170...862 MHz 2 dB R signal88...110 MHz 2 dB SAT signal950...2200 MHz
Dc Current Flow	Yes
Number Of Modules	2 modules
Material	Zamak: fixing frame Thermoplastic ABS-UV stabilised: central plate
Surface Treatment	Untreated
Surface Finish	Glossy
Marking	With imprint
Device Mounting	Flush
Fixing Mode	Screws
Depth	42 mm
Width	74.5 mm
Height	74.5 mm
Embedding Depth	24 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Resistance To Chemical Agents	Resistant to alcohol (70 %)
	Resistant to alcohol (96 %)
	Resistant to A-Lactic Acid
	Resistant to diluted quaternary ammonium
	Resistant to diluted bleach
	Resistant to diluted ammonia
	Resistant to soapy water
	Resistant to crystal cleaner
	Resistant to hydrogen peroxide 10 volumes
	Resistant to hexane

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-25...55 °C
Standards	CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	4.1 cm
Package 1 Length	7.5 cm
Package 1 Weight	474 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	4
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	699 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information